

CCT 1000-TL D (+55°C)

Relevant Test Standards:

Cyclic Corrosion Tests:

- DIN EN ISO 11997-1:2006 Cycle B (previously VDA 621-415 maybe climatic module required)
- VW PV 1210 (climate module required)

Water Condensation Tests:

- DIN EN ISO 6270-2:2005
- BS 3900 F2
- BS 3900 F15
- ASTM D2247



Salt Spray Tests:

- DIN EN ISO 9227
- DIN 50942, DIN 53167
- ASTM B 117-73, ASTM B 287-74
- ASTM B 368-68
- ISO 7253 ISO 3678
- BS 1224, BS 2011, BS3900 F4
- BS 3900 F12
- BS 5466 Part I, BS 5466 Parts 2 + 3
- NFX 41002,
- AS 21331 Section 3.1
- SIS 1841190
- JIS Z 2371

Legend

- CH** – Constant Humidity
- AT** – Alternating Temperature
- AHT**- Alternating Humidity and Temperature
- AIR** – Forced air circulation
- AWRF** – Automatic water refill

Order Information

Basic model: CCT 1000-TL D

Article numbers:

- V.735.065.650

Sales & Support:

+49 (0) 2942 98492 0

Monday to Friday

8:00 am – 17:00 pm

Köhler-VLM Testing Technologies GmbH

Mühlenbreite 17

59590 Geseke

info@koehler-vlm.de

www.koehler-vlm.de

Specification subject to changes
Pictures might differ from original



Product Description

Compact top loading corrosion test chest developed for conducting automated cyclic corrosion tests pursuant to the most common corporate (automotive) and international corrosion standards such as:

- **DIN EN ISO 11997-1:2006 Cycle B (previously VDA 621-415)**
- **VW PV 1210 (external climate module required)**

This cabinet can also conduct standard corrosion tests:

- **DIN EN ISO 6270-2:2005 (CH, AT, AHT)**
- **ASTM D2247**
- **ISO 9227**
- **IEC 60028-2-11 KA**

Customer Benefits

- Operating temperature from ambient up to +55°C
- Time and energy savings over the operational lifetime - the bottom of the test chamber is made of steel which allows fast and uniform heat transfer making this test chamber perfectly suitable for accelerated corrosion tests
- The steel bottom of the test chamber makes the test chamber more robust and less susceptible for damages compared to the competitive products made of glass reinforced plastic
- Lower total cost of ownership compared to the competitive products where the test chamber is completely made of glass reinforced plastic (shorter test periods, better energy efficiency, easier for service and maintenance, longer life cycle, more resistive to mechanical damages)
- User friendly, intuitive and versatile controller (Jumo Dicon touch) with touch screen, data logging, Ethernet interface and password protection - most common corrosion tests are already preconfigured

CCT 1000-TL D (+55°C)

Relevant Test Standards:

Cyclic Climate Tests:

- DIN EN ISO 11997-1:2006 Cycle B (previously VDA 621-415)
- VW PV 1210 (climate module required)

Water condensation tests:

- DIN EN ISO 6270-2:2005
- BS 3900 F2
- BS 3900 F15
- ASTM D2247



Salt Spray Test:

- DIN EN ISO 9227
- DIN 50942, DIN 53167
- ASTM B 117-73, ASTM B 287-74
- ASTM B 368-68
- ISO 7253 ISO 3678
- BS 1224, BS 2011, BS3900 F4
- BS 3900 F12
- BS 5466 Part I, BS 5466 Parts 2 + 3
- NFX 41002,
- AS 21331 Section 3.1
- SIS 1841190
- JIS Z 2371
- IEC 60028-2-11 KA



Figure 1 Jumo Dicon touch controller

The following accessories are included:

- 6 rods for supporting test specimen
- 2 m exhaust hose Ø 75 mm
- 2 m drain water hose Ø 32 mm
- 1 female connector for compressed air hose (size no. 5)



Technical Specifications	
Capacity	ca. 1000 L
Inner test chamber dimensions W/D/H1/H2	ca. 1425 x 800 x 690 / 1005 mm
Outer dimensions of the casing (overall) W/D/H	ca. 1895 x 890 x 1265 mm
Required power supply	230V, 50/60Hz, 2500W
Materials used	The walls of the chamber are made of Polypropylene while the bottom is made of stainless steel and coated with ECTFE. The walls have milled openings for supporting rods
Heating	Flat Micanite heaters under the bottom of the chamber for fast and uniform heat transfer
Sensors	- 1x corrosion resistant and highly sensitive temperature sensor
Temperature stability	±0,5°C
Aeration (type AIR)	timer controlled built-in fan (capacity ca. 16 m³/h)
Controller	Jumo Dicon touch programmable controller
Weight	250 kg
Communication	Ethernet interface
Other specification	
Purity demi water / fitting	< 5 µS/cm / ¼" outer diameter
Tap water (connection type)	Always via Ion-exchanging cartridge (¾" outer diameter)
Compressed Air	6-8 bar (connection nipple size 5)
Waste water, drain	Pipe fittings (spiral hose 32mm)
Air exhaust pipe outer diameter	Pipe fitting (75 mm external diameter)
Number of supporting rods / max load	6 stainless steel rods coated with plastic / 30 kg each

Process Control

- User friendly, programmable Jumo Dicon touch controller with touch screen, data logging, Ethernet interface (separate software necessary)
- Restricted access for operators to three different operating levels
- Memory storage with the capacity to hold up to 50 test programs, most common corrosion tests are already preconfigured in the factory
- The controller steers the external climate module for the tests that require air conditioning (typically PV 1210)
- Full overview of all digital and analog inputs / outputs


Operating System Water Condensation (CH) according to ISO 6270-2

- Flat heaters under the bottom of the chamber for uniform and rapid heating of the water in the trough
- Temperature stability inside the chamber ±0,5°C
- Automatic refilling of the test chamber (AWRF) for maintaining the constant water level in the trough
- Parameters for standard water condensation tests are already preconfigured

Operating System Aeration

- Aeration with environmental air drying
- Adjustable air distribution system inside the test chamber for uniform drying of the test specimens
- Fan with controllable rotation speed
- **Option:** Air conditioning module for providing standard climate acc. to DIN 50014 (ISO 554): 23°C ±2°C and 50% ±5% RH

CCT 1000-TL D (+55°C)



Operating System Salt Spray (according to ISO 9227)

- Electronically controlled diaphragm pump for accurate flow control of test solution
- Adjustable high performance acrylic spray nozzle for optimal generation and distribution of the salt fog
- Transparent humidifier made of heat resistant Borosilicate glass with a replaceable PE air filter
- Safety air pressure valve on the humidifier
- Over temperature protection of the humidifier
- Air purge function for rapid evacuation of the salt fog out of the chamber
- **Accessories:** 210 L PE storage reservoir for test solution (level indicator optional)
- **Option:** Nozzle for washing the test chamber after the salt spray test is finished




Figure 2 Dimension CCT 1000-TL D